


Product Code: CMA012AG

Luckinslive 391934979

Description: 10AX 2 Gang 2 Way Plate Switch



### General Information

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
MiniGrid Plate (Gang)	1	
MiniGrid Single Width Module Quantity	2	
MiniGrid Double Width Module Quantity	1	
Style	Rounded Profile	
Colour	Anthracite Grey	
Switch Finish	Polar White	
Materials	Front Plate & Rocker Switch: Urea	Rear Housing: Nylon
	Terminals: Brass	Terminal Screws: Steel & Yellow Passivated
	Contacts: Silver "on-lay" Copper / Brass	Internal Busbars: Formed Pressed Brass
Anti Microbial Certified	Yes	
Operating Voltage (AC)	250	Frequency (Hz) 50
Inductive Load Rating (AX)	10	
Load Rating Comments	Suitable for Fluorescent or Inductive Loads	
Termination Type	Screw	
Terminal Size (mm)	Ø3.5	Terminal Torque Value (Nm) 0.5
Terminal Capacity - Solid (mm²)	4 x 1.5 or 2 x 2.5	
Modular Rocker Switches	Yes	
2 Way Switch	Yes	
Minimum Back Box Depth (mm)	16	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	25	

**Standards** BS EN 60669-1

### Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.

Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product. Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.

All white & grey moulded accessories are manufactured using Urea Formaldehyde, which has similar inherent properties to antimicrobial additives that inhibit the growth of infectious diseases as well as anti-viral properties against enveloped and non-enveloped viruses.

All products have been independently tested with 99.9% of enveloped viruses and 92% of non-enveloped viruses killed off whilst achieving a 99.9% kill rate across all four types of the strains of bacteria - MRSA, E-Coli, Salmonella, and Klebsiella Pneumoniae.

Interchangeable with modules in the MiniGrid Range.



CLICK OR SCAN

Catalogue



Range



DoC



Installation



CLICK OR SCAN